

## Arova Spritzbeize

1014

Solvent-based **hardwood stain** for pore accentuated effects for industrial and professional use.

### PRODUCT DESCRIPTION

#### General

Solvent-based spray stain for a porous stain appearance; quick drying, high light fastness, no roughening of the wood. The product can be coated with water-based and solvent-based wood varnishes.

#### Special properties and standards



- **French ordinance DEVL1104875A**  
Marking of construction coating products for their emission of volatile pollutants: A+

#### Application area



For furniture, interior fixtures, wall paneling and wood ceilings.

Depending on the furniture coating used, the product is suitable for surfaces of furnitures and interior finishing in application areas II – IV according to ÖNORM A 1610-12.

Application in combination with a suitable topcoat system.

### PROCESSING

#### Processing instructions



- Please stir product well before and during use.
- The temperature of the product and object, and the room temperature must be at least + 15 °C.
- Ensure an even stain application!
- A staining application with Airmix or Airless low pressure device is also possible.
- Apply evenly and with a small excess by spraying so that the surfaces appear damp.
- The product cannot be dispersed.
- Less absorbent wood types require less application compared to more absorbent timber.
- Various types of wood such as Oak contain water-soluble substances, which become active when overcoating with water-based furniture coatings. To prevent discolouration or marks when painting wood rich in active substances we therefore recommend priming them first with Aduro Primer (2523).
- Do not return the product from the application tool or product contaminated with wood dust to the original container.

- Any change in the processing sequence, environmental conditions, non-observance of instructions or the use of products not listed may have an unfavourable effect on the result.
- Please observe our **ARL 110 - Working guidelines for staining Wood**.

### Application technique



	Cup gun
Spraying nozzle Ø (mm)	1,5
Spraying pressure (bar)	1,5 - 2,5
Yield per application (m <sup>2</sup> /l)	8
Applied quantity per application (g/m <sup>2</sup> )	40 - 50

The stated yield includes spray loss.

The shape and surface condition of the workpiece as well as the type of application influence the actual consumption. Accurate values for consumption must be obtained by applying trial coats in advance.

### Drying times

(at 23 °C and 50 % rel. humidity)




Recoatable (solvent-based coatings)	15 minutes
Recoatable (water-based coatings)	1 hour(s)

If necessary, a forced drying is also possible.

The figures given above are reference values. The drying time depends on the type of substrate, coat thickness, temperature, air exchange and relative atmospheric humidity.

### Cleaning the working equipment



With Waschverdünner (8501) or Nitro-Verdünner (8017) immediately after use.

## SUBSTRATE

### Type of substrate

Fine and coarse-pored hardwoods such as oak, ash, walnut, mahogany, etc.

### Substrate property

The substrate must be dry, clean, capable of holding the paint, and it must be free of grease and wax and free from wood dust.

### Substrate preparation

Grit size 150 – 180

Thoroughly remove sanding dust, especially from the wood pores.

It is not necessary to wet the wood before staining.

## COATING SYSTEM

### Stain application

Apply uniformly along the direction of the wood fiber using the wet on wet method with slight excess so that the surfaces appear slightly moist.

### Subsequent coating

The product can be coated with both water- and solvent-based ADLER furniture coatings. For light stain shades and color tones, we generally recommend the use of lightfast varnishes such as Bluefin Resist, Aduro Legnopur. When using non-lightfast types of paint, it can be expected that the final color will appear slightly yellowish; this effect increases with aging.


For white stained surfaces we recommend to apply additionally one layer of Legnopur, tinted with 1.0 % up to a max. of 3.0 % Solva-Tint Polarweiß (9035040114). Alternatively, a water-based furniture varnish such as Bluefin Top-Antiscratch, tinted with 1.0 to max. 3.0 % Aqua-Tint Polarweiß (9009040114), can be used. Avoid overlapping when spraying!

## ORDERING INFORMATION

### Size of trading unit

0.9l, 4l

### Colour shades / Glosslevels



1014400100

#### Standard colour(s):

Farblos (1014400100)  
 Weiß (1014043001)  
 Hanf (1014043002)  
 Honig (1014043003)  
 Rustikal (1014043004)  
 Kognak (1014043005)  
 Maron (1014043006)  
 Tabak (1014043007)  
 Schilf (1014043008)  
 Nuss (1014043009)  
 Palisander (1014043010)  
 Stein (1014043011)  
 Schwemmholz (1014043012)  
 Alteiche (1014043013)  
 Olive (1014043014)  
 Schwarz (1014043015)

All colours can be mixed with each other and, if required, diluted with Arova Spritzbeize Farblos (1014400100).

If it is thinned excessively, the inherent color of the wood and the natural yellowing of the wood can lead to noticeable color changes over a period of time. The color changes if the liquid stain comes into contact with metal.

Prior to applying the stain and the coating, you should always stain a sample on the original wood and treat it with the intended coating material in order to assess the final colour shade. Only use stains from the same batch for a commission.

### Supplementary products

Aduro Legnopur (2513)  
 Aduro Primer (2523)  
 Aqua-Tint Polarweiß (9009040114)  
 Bluefin Resist (2963)  
 Bluefin Top-Antiscratch (2960)  
 Nitro-Verdünner 8017 (8017)  
 Solva-Tint Polarweiß (9035040114)  
 Waschverdünner 8501 (8501)

Please refer to the corresponding technical data sheets of the products.

---

**FURTHER DETAILS**

---

**Durability / storage**

Min. 1 year(s) in the original sealed containers.  
Cool, but frost-free.

---

**Safety information**

The product is only suitable for the industrial and professional use.

The inhalation of paint aerosols during spray application must generally be avoided. This is ensured by the proper use of a respirator (combination filter A2/P2).

Further information on the subject of safety during transport, storage and handling as well as disposal can be found in the relevant safety data sheet. The current version can be accessed on the Internet at [www.adler-lacke.com](http://www.adler-lacke.com).

---